

Metalik® Inkjet Rose Gold 076SRG

High-Tack Printable Metallic Polyester Films

Applications

- Suitable for permanent lamination onto display boards & other smooth surfaces
- POS decoration with or without print
- Ideal for shop-fitting, perfumeries, luxury boutiques, and Christmas campaigns
- Turn any smooth surface into metallic
- Ideal for packaging with metallic effect, our silver film is recommended for Color Logic® software
- Combine permanent print and CAD applications, for example doming
- Also available in Metallic Silver & Gold

Benefits

- Shiny Silver reverse-side, bright shiny Rose Gold front-side
- Perfect film for lamination on boards, for example Dibond
- Very smooth finish, close to mirror effect
- High-tack adhesive for strong permanent adhesion
- Can be cut and weeded

Post Printing Information for Latex & Solvent Inks:

As with all filmic media, this product must be allowed to “gas-out” after printing. This can be achieved by leaving the prints face up, ideally 24+ hours, to set, dry and harden. If unable to do this e.g. with a long print run: after printing the roll stand it vertically and loosely unwind the printed roll as much as possible, to allow air in and gases/solvents out.

Recommended Conditions:

Printroom	15°C - 30°C	30% - 65% RH
Usage	-40°C - 80°C	10% - 90% RH
Storage	10°C - 20°C	20% - 50% RH



KERNOW COATINGS | Kernick Road | Penryn | Cornwall | TR10 9DQ | UK

www.kernowcoatings.com | sales@kernowcoatings.com | T: +44 (0)1326373147

Registered in England | No. 1092182 | A Member of the Sensitisers Group of Companies

The information provided herein is correct to the best of our knowledge. No liability for any errors, facts or opinions is accepted. We recommend users make their own assessments to satisfy themselves as to the suitability of this product for their application. Copyright Sensitisers Group 2017



Printability:



Face Thickness without Adh:

55 μ	2.2 mil	76 gsm
---------	------------	-----------

Available widths:

1372 54"	1524 60"
-------------	-------------

Adhesion:

AFTER 24H 25+ N /25mm
